Certificate

No. c7337a-22

Customer:

DEHN SE + Co KG
Hans-Dehn-Str. 1
92318 Neumarkt, Germany

Class EA

Test sample(s):

Data cable:
KERPEN DATACOM MegaLine® F10-130 S/F
Part no.: LKD7KS700010000

Balanced cord:
Telegärtner patch cord PC RJ45(V1)-RJ45(V1) SFTP C6A LSZH
Part no.: L0000xyzzzz

Connecting hardware:
METZ CONNECT C6Amodul
Part no.: 130B11-E 180°

Surge Protective Device:
DEHNpatch DPA CL8 EA
Part no.: 929161

Applied standard(s):

ISO/IEC 11801-1 Ed.1.0 (2017-11)

Result(s):

The sample meets the limits of the specified standards and regulations with respect to the parameters indicated above.

4 Connector Channel, Copper, Class EA

GHMT Type Approval

The test results which were determined in the course of the measurement refer to the submitted specimen. Any future technical modifications of the verified products are subject to the responsibility of the manufacturer.

This Certificate refers to the comprehensive test report **no. R7337a-22** and shall only be applicable in conjunction with the test report. This certificate is valid 24 months after date of testing.

Bexbach, 06. May 2022

Dirk Wilhelm, engineer
(Chairman of the Managing Board)

Test laboratory accredited by DAkkS in accordance with DIN EN ISO/IEC 17025:2018.
*The accreditation is valid for the test methods listed in certificate **D-PL-17559-01-00**.*

GHMT AG
In der Kolling 320
66450 Bexbach / Germany

PO box 11 16
66442 Bexbach / Germany

T: +49 6826 92 28-0
F: +49 6826 92 28-290

info@ghmt.de
www.ghmt.de

RELIABILITY IN TOTAL
REQUIRES ACCURACY IN DETAIL.