

**AF 10 V4A 1500 (860 115)**





Figure without obligation



Made of corrosion-resistant stainless steel (V4A), for connecting down conductors to the earth-termination system.

Type	AF 10 V4A 1500
Part No.	860 115
Material	StSt (V4A)
Material No.	1.4571 / 1.4404
ASTM / AISI:	316Ti / 316L
Length (l1)	1500 mm
Dimensions	Ø10 mm
Cross-section	78 mm <sup>2</sup>
Standard	EN 62561-2
Weight	930 g
Customs tariff number (Comb. Nomenclature EU)	72222031
GTIN	4013364101104
PU	5 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.

Other dimensions are available upon request.