


**TE 20 1000 AZ V4A (620 903)**



Figure without obligation



Type	TE 20 1000 AZ V4A
Part No.	620 903
Component protection	German Patent No. P 32 22 201.7
Material	StSt (V4A)
Material No.	1.4571 / 1.4404 / 1.4401
ASTM / AISI:	316Ti / 316L / 316
Rod length (l1)	1000 mm
Diameter Ø (d1)	20 mm
Pin diameter	10 / 13 mm
Tensile strength	500-730 N/mm <sup>2</sup>
Specific conductivity	≥ 1.25 m/Ohm mm <sup>2</sup>
Specific resistance	≤ 0.8 Ohm mm <sup>2</sup> / m
Short-circuit current (AC 50 Hz / DC) (1 s; ≤ 300 °C)	4.2 kA
Standard	EN 62561-2
Weight	2,43 kg
Customs tariff number (Comb. Nomenclature EU)	85389099
GTIN	4013364342859
PU	6 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.