


BXT ML2 BD DL S 15 (920 243)


- Suitable for Dupline buses
- LifeCheck SPD monitoring function
- Effective protection for one pair and shield
- For installation in conformity with the lightning protection zone concept at the boundaries from $0_A -2$ and higher



Figure without obligation



Basic circuit diagram BXT ML2 BD S 15



Dimension drawing BXT ML2 BD S 15

Space-saving combined lightning current and surge arrester module with LifeCheck feature for protecting one pair of unearthed balanced interfaces, which specifically fulfils the requirements of Dupline buses, direct or indirect shield earthing. If LifeCheck detects thermal or electrical overload, the arrester has to be replaced. This status is indicated contactlessly by the DEHNrecord LC / SCM / MCM reader.

Type	BXT ML2 BD DL S 15
Part No.	920 243
SPD monitoring system	LifeCheck
SPD class	TYPE II
Nominal voltage (U_N)	15 V
Max. continuous operating voltage (d.c.) (U_C)	17 V
Max. continuous operating voltage (a.c.) (U_C)	12 V
Nominal current at 70 °C (I_n)	0.4 A
D1 Total lightning impulse current (10/350 μ s) (I_{imp})	9 kA
D1 Lightning impulse current (10/350 μ s) per line (I_{imp})	2.5 kA
C2 Total nominal discharge current (8/20 μ s) (I_n)	20 kA
C2 Nominal discharge current (8/20 μ s) per line (I_n)	10 kA
Voltage protection level line-line for I_{imp} D1 (U_P)	≤ 30 V
Voltage protection level line-PG for I_{imp} D1 (U_P)	≤ 550 V
Voltage protection level line-line at 1 kV/ μ s C3 (U_P)	≤ 24 V
Voltage protection level line-PG at 1 kV/ μ s C3 (U_P)	≤ 550 V
Series resistance per line	2.2 ohm(s)
Cut-off frequency line-line (f_c)	2.7 MHz
Capacitance line-line (C)	≤ 1.9 nF
Capacitance line-PG (C)	≤ 25 pF
Operating temperature range (T_U)	-40 °C ... +80 °C
Degree of protection (with plugged-in protection module)	IP 20
Pluggable into	BXT BAS / BSP BAS 4 base part
Earthing via	BXT BAS / BSP BAS 4 base part
Enclosure material	polyamide PA 6.6
Colour	yellow
Test standards	IEC 61643-21 / EN 61643-21
Approvals	ATEX, IECEx, CSA & USA Hazloc, SIL
SIL classification	up to SIL3 ^{*)}
ATEX approvals	DEKRA 11ATEX0089 X: II 3 G Ex nA IIC T4 Gc
IECEx approvals	DEK 11.0032X: Ex nA IIC T4 Gc
CSA & USA Hazloc approvals (1)	2516389: Class I Div. 2 GP A, B, C, D T4
CSA & USA Hazloc approvals (2)	2516389: Class I Zone 2, AEx nA IIC T4
China Compulsory Certification	CCC No. 2021312304001155
Weight	21 g
Customs tariff number (Comb. Nomenclature EU)	85363010
GTIN	4013364126732
PU	1 pc(s)

^{*)}For more detailed information, please visit www.dehn-international.com.

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.