


DG MOD CI 275 (952 020)


- High discharge capacity due to heavy-duty zinc oxide varistors / spark gaps
- Easy replacement of protection modules without tools due to module locking system with module release button



Figure without obligation



Basic circuit diagram DG MOD CI 275



Dimension drawing DG MOD CI 275

Protection module for DEHNguard M ... CI 275 surge arresters comprising a varistor connected in series with the integrated backup fuse.

Type	DG MOD CI 275
Part No.	952 020
Nominal discharge current (8/20 μ s) (I_n)	12.5 kA
Max. discharge current (8/20 μ s) (I_{max})	25 kA
Max. continuous operating voltage (a.c.) (U_c)	275 V
Weight	52 g
Customs tariff number (Comb. Nomenclature EU)	85363030
GTIN	4013364127784
PU	1 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.