


DG MOD 275 (952 010)


- High discharge capacity due to heavy-duty zinc oxide varistors / spark gaps
- Easy replacement of protection modules without tools due to module locking system with module release button



Figure without obligation



Basic circuit diagram DG MOD 275



Dimension drawing DG MOD 275

Varistor-based protection module for DEHNguard M ... and DEHNguard S ... surge arresters.

| Type | DG MOD 275 |
|---|---------------|
| Part No. | 952 010 |
| Nominal discharge current (8/20 μ s) (I_n) | 20 kA |
| Max. discharge current (8/20 μ s) (I_{max}) | 40 kA |
| Max. continuous operating voltage (a.c.) (U_c) | 275 V |
| Weight | 43 g |
| Customs tariff number (Comb. Nomenclature EU) | 85363030 |
| GTIN | 4013364108356 |
| PU | 1 pc(s) |

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.