

BXT ML2 BE S 48 (920 225)

- LifeCheck SPD monitoring function
- Optimal protection of two single lines and the cable shield
- For use in conformity with the lightning protection zone concept at the boundaries from 0_A –2 and higher




Figure without obligation

Basic circuit diagram BXT ML2 BE S 48

Dimension drawing BXT ML2 BE S 48

Space-saving combined lightning current and surge arrester module with LifeCheck feature for protecting two single lines with common reference potential as well as unbalanced interfaces, with direct or indirect shield earthing. If LifeCheck detects thermal or electrical overload, the arrester has to be replaced. This status is indicated contactlessly by the DEHNrecord LC / SCM / MCM reader.

Type	BXT ML2 BE S 48
Part No.	920 225
SPD monitoring system	LifeCheck
SPD class	TYPE 1 P1
Nominal voltage (U _N)	48 V
Max. continuous operating voltage (d.c.) (U _C)	54 V
Max. continuous operating voltage (a.c.) (U _C)	38.1 V
Nominal current at 45 °C (I _N)	0.75 A
D1 Total lightning impulse current (10/350 µs) (I _{imp})	9 kA
D1 Lightning impulse current (10/350 µs) per line (I _{imp})	2.5 kA
C2 Total nominal discharge current (8/20 µs) (I _n)	20 kA
C2 Nominal discharge current (8/20 µs) per line (I _n)	10 kA
Voltage protection level line-line for I _{imp} D1 (U _p)	≤ 160 V
Voltage protection level line-PG for I _{imp} D1 (U _p)	≤ 95 V
Voltage protection level line-line at 1 kV/µs C3 (U _p)	≤ 140 V
Voltage protection level line-PG at 1 kV/µs C3 (U _p)	≤ 70 V
Series resistance per line	1.8 ohm(s)
Cut-off frequency line-PG (f _c)	8.7 MHz
Capacitance line-line (C)	≤ 0.35 nF
Capacitance line-PG (C)	≤ 0.7 nF
Operating temperature range (T _U)	-40 °C ... +80 °C
Degree of protection (with plugged-in protection module)	IP 20
Pluggable into	BXT BAS / BSP BAS 4 base part
Earthing via	BXT BAS / BSP BAS 4 base part
Enclosure material	polyamide PA 6.6
Colour	yellow
Test standards	IEC 61643-21 / EN 61643-21
Approvals	CSA, UL 497B, ATEX, IECEx, CSA & USA Hazloc, SIL
SIL classification	up to SIL3 ^{*)}
ATEX approvals	DEKRA 11ATEX0089 X: II 3 G Ex nA IIC T4 Gc
IECEx approvals	DEK 11.0032X: Ex nA IIC T4 Gc
CSA & USA Hazloc approvals (1)	2516389: Class I Div. 2 GP A, B, C, D T4
CSA & USA Hazloc approvals (2)	2516389: Class I Zone 2, AEx nA IIC T4
China Compulsory Certification	CCC No. 2021312304001155
Weight	21 g
Customs tariff number (Comb. Nomenclature EU)	85363010
GTIN	4013364118379
PU	1 pc(s)

^{*)}For more detailed information, please visit www.dehn-international.com.

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.