


DCOR L 2P 320 (900 432)

- Visual fault indication
- Compact design
- For use in flush-mounted systems, cable ducts and flush-type boxes



Two-pole surge arrester for all installation systems (1+1 configuration) and luminaires of protection class I; compact design.

Technical data

Type	DCOR L 2P 320
Part No.	900 432
SPD according to EN 61643-11 / IEC 61643-11	type 2 / class II
Energy coordination with terminal equipment (≤ 10 m)	type 2 + type 3
Nominal voltage (a.c.) (U _N)	230 / 277 V (50 / 60 Hz)
Max. continuous operating voltage (a.c.) [L-N] (U _C)	320 V (50 / 60 Hz)
Max. continuous operating voltage (a.c.) [N-PE] (U _C)	255 V (50 / 60 Hz)
Nominal discharge current (8/20 μs) (I _n)	5 kA
Max. discharge current (8/20 μs) (I _{max})	10 kA
Total discharge current (8/20 μs) [L+N-PE] (I _{total})	20 kA
Voltage protection level [L-N] (U _P)	≤ 1.75 kV
Voltage protection level [N-PE] (U _P)	≤ 1.5 kV
Follow current extinguishing capability [N-PE] (I _f)	100 A _{rms}
Response time [L-N] (t _A)	≤ 25 ns
Response time [L/N-PE] (t _A)	≤ 100 ns
Max. mains-side overcurrent protection	25 A gG
Short-circuit withstand capability for mains-side overcurrent protection (I _{SCCR})	25 kA _{rms}
Temporary overvoltage (TOV) [L-N] (U _T) – Characteristic	335 V / 5 sec. – withstand
Temporary overvoltage (TOV) [L-N] (U _T) – Characteristic	440 V / 120 min. – safe failure
Temporary overvoltage (TOV) [N-PE] (U _T) – Characteristic	1200 V / 200 ms – withstand
Operating state / fault indication	green / red
Number of ports	1
Operating temperature range (T _U)	-40 °C ... +80 °C
Connecting wires	1.5 mm ² , Length: 230 mm (L, N) / 240 mm (PE)
Enclosure material	thermoplastic, red, UL 94 V-2
Place of installation	indoor installation
Degree of protection of installed device	IP 20
Approvals	KEMA
Weight	61 g
Customs tariff number (Comb. Nomenclature EU)	85363030
GTIN	4013364157309
PU	1 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.