
DG MOD NPE (952 050)


- High discharge capacity due to heavy-duty zinc oxide varistors / spark gaps
- Easy replacement of protection modules without tools due to module locking system with module release button
- The plug-in protection module can be replaced without the need to de-energise and without removing the distribution board cover



Figure without obligation



Basic circuit diagram DG MOD NPE



Dimension drawing DG MOD NPE

N-PE spark-gap-based protection module for two-pole and four-pole DEHNguard DG M TT ... surge arresters.

Type Part No.	DG MOD NPE 952 050
Nominal discharge current (8/20 µs) (I_n)	20 kA
Max. discharge current (8/20 µs) (I_{max})	40 kA
Max. continuous operating voltage (a.c.) (U_C)	255 V
Weight	38 g
Customs tariff number (Comb. Nomenclature EU)	85363030
GTIN	4013364108370
PU	1 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.