


BXT ML4 BD 180 (920 347)

- LifeCheck SPD monitoring function
- Optimal protection of two pairs
- For installation in conformity with the lightning protection zone concept at the boundaries from 0_A –2 and higher



Space-saving combined lightning current and surge arrester module with LifeCheck feature for protecting two pairs of unearthed balanced interfaces. If LifeCheck detects thermal or electrical overload, the arrester has to be replaced. This status is indicated contactlessly by the DEHNrecord LC / SCM / MCM reader.

Type	BXT ML4 BD 180
Part No.	920 347
SPD monitoring system	LifeCheck
SPD class	TYPE 1 P2
Nominal voltage (U _N)	180 V
Max. continuous operating voltage (d.c.) (U _C)	180 V
Max. continuous operating voltage (a.c.) (U _C)	127 V
Nominal current at 45 °C (I _N)	0.75 A
D1 Total lightning impulse current (10/350 µs) (I _{imp})	10 kA
D1 Lightning impulse current (10/350 µs) per line (I _{imp})	2.5 kA
C2 Total nominal discharge current (8/20 µs) (I _n)	20 kA
C2 Nominal discharge current (8/20 µs) per line (I _n)	10 kA
Voltage protection level line-line for I _{imp} D1 (U _p)	≤ 270 V
Voltage protection level line-PG for I _{imp} D1 (U _p)	≤ 550 V
Voltage protection level line-line at 1 kV/µs C3 (U _p)	≤ 250 V
Voltage protection level line-PG at 1 kV/µs C3 (U _p)	≤ 550 V
Series resistance per line	1.8 ohm(s)
Cut-off frequency line-line (f _c)	25.0 MHz
Capacitance line-line (C)	≤ 240 pF
Capacitance line-PG (C)	≤ 16 pF
Operating temperature range (T _U)	-40 °C ... +80 °C
Degree of protection (with plugged-in protection module)	IP 20
Pluggable into	BXT BAS / BSP BAS 4 base part
Earthing via	BXT BAS / BSP BAS 4 base part
Enclosure material	polyamide PA 6.6
Colour	yellow
Test standards	IEC 61643-21 / EN 61643-21
Approvals	CSA, UL 497B, ATEX, IECEx, CSA & USA Hazloc, SIL
SIL classification	up to SIL3 ^{*)}
ATEX approvals	DEKRA 11ATEX0089 X: II 3 G Ex nA IIC T4 Gc
IECEx approvals	DEK 11.0032X: Ex nA IIC T4 Gc
CSA & USA Hazloc approvals (1)	2516389: Class I Div. 2 GP A, B, C, D T4
CSA & USA Hazloc approvals (2)	2516389: Class I Zone 2, AEx nA IIC T4
China Compulsory Certification	CCC No. 2021312304001155
Weight	24 g
Customs tariff number (Comb. Nomenclature EU)	85363010
GTIN	4013364109018
PU	1 pc(s)

^{*)}For more detailed information, please visit www.dehn-international.com.

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.