



SEIL 9 50Q CUGALSN R100M (832 839)



Figure without obligation

Copper cable, tinned, according to EN 62561-2 for lightning protection and earth-termination systems or equipotential bonding.

Type	SEIL 9 50Q CUGALSN R100M
Part No.	832 839 ✓
Cross-section	50 mm ²
Cable structure qty x Ø wire	19 x 1.8 mm
Material	Cu/gal Sn
Average of tin layer thickness	2 µm
Standard	EN 62561-2
Outside diameter Ø	9 mm
Conductivity	≥ 52.63 m / Ohm mm ²
Resistivity	≤ 0.019 Ohm mm ² / m
Short-circuit current (a.c. 50 Hz / d.c.) (1 s; ≤ 150 °C)	7.2 kA
Length tolerance	+/- 5%
Weight	438 g/m
Customs tariff number (Comb. Nomenclature EU)	74130000
GTIN	4013364093164
PU	100 m

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.

Cables in different dimensions and materials are available upon request.