


DGA FF TV (909 703)


- Frequency range for analogue and digital TV, also suitable for reverse LAN channels
- Arresters of type FF and GFF with integrated measuring output
- Three types for adapted use in conformity with the lightning protection zone concept at the boundaries from $0_A - 2$ (combined lightning current and surge arresters of type GFF), $0_A - 1$ (lightning current arresters of type GF) and $1 - 2$ (surge arresters of type FF)



Figure without obligation



Basic circuit diagram DGA FF TV



Dimension drawing DGA FF TV

DGA ... TV arresters with F connection for remote supply protect 75-ohm satellite and broadband cable systems and fulfil the high shielding requirements of class A according to EN 50083-2. They allow space-saving installation in all common TV and satellite applications and are available as lightning current arresters, surge arresters as well as combined lightning current and surge arresters with integrated measuring output, allowing the system to be easily tested.

Type	DGA FF TV
Part No.	909 703
SPD class	TYPE 3P1
Max. continuous operating voltage (d.c.) (U_c)	24 V
Nominal current (I_n)	2 A
D1 Lightning impulse current (10/350 μ s) (I_{imp})	0.2 kA
C2 Nominal discharge current (8/20 μ s) (I_n)	1.5 kA
Voltage protection level for I_{imp} D1 (U_p)	\leq 230 V
Voltage protection level for I_n C2 (U_p)	\leq 300 V
Voltage protection level at 1 kV/ μ s C3 (U_p)	\leq 60 V
Frequency range	d.c. / 5-3000 MHz
Insertion loss 5-862 MHz typ.	1.2 dB
Insertion loss 862-2400 MHz typ.	1.4 dB
Insertion loss 2400-3000 MHz typ.	2 dB
Return loss	\geq 14 dB
Return loss (47-2400 MHz)	\geq 18 dB (-1.5 dB/octave)
Return loss test socket (5-47 MHz)	\geq 18 dB
Test socket connection loss	20 dB
Shield attenuation 5-300 MHz	\geq 85 dB
Shield attenuation 300-470 MHz	\geq 80 dB
Shield attenuation 470-1000 MHz	\geq 75 dB
Shield attenuation 1000-2400 MHz	\geq 55 dB
Characteristic impedance (Z)	75 ohms
Operating temperature range (T_U)	-40 °C ... +80 °C
Degree of protection (if lines are connected)	IP 30
For mounting on	35 mm DIN rails acc. to EN 60715 or wall mounting
Connection (input / output)	F socket / F socket
Earthing via	DIN rail or screw connection
Enclosure material	metal
Colour	bare surface
Test standards	IEC 61643-21 / EN 61643-21
Approvals	EAC
Accessories	2x F plugs
Weight	233 g
Customs tariff number (Comb. Nomenclature EU)	85363010
GTIN	4013364085664
PU	1 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.