

DG MU CGD 480 3W+G (908 204)

- Prewired complete unit without the need for additional overcurrent protection devices
- High discharge capacity due to heavy-duty zinc oxide varistors (I_{max} 50 kA 8x20 μ s)
- Short circuit current rating (SCCR) 200 kA
- ANSI/UL 1449 – 4th Ed. Open-Type 1 SPD






Figure without obligation



Basic circuit diagram DG MU CGD 480 3W+G



Dimension drawing DG MU CGD 480 3W+G

DIN rail mount, pluggable surge arrester consisting of a base part and plug-in protection modules for application in Corner Grounded Delta systems

Type	DG MU CGD 480 3W+G
Part No.	908 204
SPD classification acc. to ANSI/UL 1449 4 th Ed.	Open-Type 1 SPD
SPD classification acc. to CSA - C22.2 No. 269.1-14	Type 4-1 Component Assembly
Nominal System Voltage [L-G] / [L-L] (U_N)	240 V a.c. / 480 V a.c.
Nominal Power System Frequency	50 / 60 Hz
Max. continuous operating voltage AC [L-G] / [L-L] (MCOV)	550 V a.c. / 1100 V a.c.
Nominal discharge current (8x 20 μ s) (I_n)	20 kA
Max. discharge current (8/20) (I_{max})	50 kA
Voltage Protection Rating [L-G] / [L-L] (VPR)	1800 V _{pk} / 3000 V _{pk}
Max. mains-side overcurrent protection	Not needed
Short Circuit Current Rating (SCCR)	200 kA
System Type	Corner Grounded Delta
Operating Temperature Range (T_U)	-35°C...+85°C
Operating state / fault indication	Green = Good ; Red = Replace Module
Cross-sectional area (min.)	14 AWG / 2.5 mm ²
Cross-sectional area (max.)	4 AWG / 25 mm ²
Terminal Torque Ratings	35-45 Lbs-in
Mounting	35 mm Hutschiene nach EN 60715
Enclosure material	Thermoplast, Farbe rot, UL 94 V-0
Degree of protection	IP 20
Capacity	2 module(s), DIN 43880
Approvals	UL, CSA
Weight	259 g
Customs tariff number (Comb. Nomenclature EU)	85363030
GTIN	4013364148666
PU	1 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.